

The performance information listed is for new products and is intended to be used for reference only, and is not complete. Depending on the components, accessories, and options chosen, the actual rating could vary. Confirm ratings for specific products with your supplier or JELD-WEN sales representative.

Flat Casing Vinyl												
SERIES	GLAZING	SPACER	No Grids				Flat GBG, Narrow Contour GBG			Wide Contoured Grids		
			U-VALUE	CR	SHGC	VT	U-VALUE	SHGC	VT	U-VALUE	SHGC	VT
Double-Hung Tilt DP 20	Clear	Intercept	0.49	42	0.60	0.63	0.49	0.54	0.56	0.49	0.54	0.56
	Low-E 272	Intercept	0.35	51	0.32	0.55	0.35	0.29	0.49	0.37	0.29	0.49
	Low-E 272 Argon	Intercept	0.32	54	0.32	0.55	0.32	0.29	0.49	0.34	0.29	0.49
	Low-E 366	Intercept	0.35	52	0.21	0.49	0.35	0.19	0.44	0.37	0.19	0.44
	Low-E 366 Argon	Intercept	0.32	55	0.21	0.49	0.32	0.19	0.44	0.33	0.19	0.44
Double-Hung Tilt DP 50	Clear	Intercept	0.49	42	0.60	0.63	0.49	0.54	0.56	0.50	0.54	0.56
	Low-E 272	Intercept	0.36	51	0.32	0.55	0.36	0.29	0.49	0.37	0.29	0.49
	Low-E 272 Argon	Intercept	0.32	54	0.32	0.55	0.32	0.29	0.49	0.34	0.29	0.49
	Low-E 366	Intercept	0.35	52	0.21	0.49	0.35	0.19	0.44	0.37	0.19	0.44
	Low-E 366 Argon	Intercept	0.32	54	0.21	0.49	0.32	0.19	0.44	0.33	0.19	0.44
Casement	Clear	Intercept	0.42	43	0.56	0.59	0.42	0.50	0.52	0.42	0.50	0.52
	Low-E 272	Intercept	0.31	54	0.30	0.51	0.31	0.27	0.45	0.32	0.27	0.45
	Low-E 272 Argon	Intercept	0.29	56	0.30	0.51	0.29	0.27	0.45	0.30	0.27	0.45
	Low-E 366	Intercept	0.31	54	0.20	0.46	0.31	0.18	0.41	0.32	0.18	0.41
	Low-E 366 Argon	Intercept	0.29	56	0.20	0.46	0.29	0.18	0.41	0.30	0.18	0.41
Stationary Casement	Clear	Intercept	0.44	43	0.61	0.63	0.44	0.54	0.56	0.44	0.54	0.56
	Low-E 272	Intercept	0.30	53	0.32	0.55	0.30	0.29	0.49	0.32	0.29	0.49
	Low-E 272 Argon	Intercept	0.28	55	0.32	0.55	0.28	0.29	0.49	0.30	0.29	0.49
	Low-E 366	Intercept	0.30	54	0.21	0.50	0.30	0.19	0.44	0.32	0.19	0.44
	Low-E 366 Argon	Intercept	0.28	56	0.21	0.50	0.28	0.19	0.44	0.29	0.19	0.44
Awning	Clear	Intercept	0.42	43	0.51	0.53	0.42	0.46	0.47	0.42	0.46	0.47
	Low-E 272	Intercept	0.31	52	0.27	0.46	0.31	0.25	0.41	0.32	0.25	0.41
	Low-E 272 Argon	Intercept	0.29	55	0.27	0.46	0.29	0.30	0.25	0.30	0.25	0.41
	Low-E 366	Intercept	0.31	53	0.18	0.41	0.31	0.32	0.17	0.32	0.17	0.37
	Low-E 366 Argon	Intercept	0.29	55	0.18	0.41	0.29	0.30	0.16	0.30	0.16	0.37